


ANALISIS GRANULOMETRICOS

MUESTRA: IP38

UTM X: 640042


UTM Y: 3221692



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 (0 %C)	0.0%	100.0%
n°10	2 mm	0.06 (0 %C)	0.1%	99.9%
n°18	1 mm	0.12 (25 %C)	0.2%	99.8%
n°25	0.71 mm	1.96 (25 %C)	2.1%	97.9%
n°35	0.5 mm	14.38 (0 %C)	16.5%	83.5%
n°60	0.25 mm	63.69 (0 %C)	80.2%	19.8%
n°80	0.18 mm	13.23 (0 %C)	93.4%	6.6%
n°120	0.125 mm	6.04 (0 %C)	99.5%	0.5%
n°230	0.063 mm	0.46 (0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.06 (0 %C)	100.0%	0.0%

% FINOS	0.06%
% CASCAJO	0.52%
D16	0.501
D50	0.368
D84	0.229
Media	0.366
σ	0.136
M. distribuc.	0.365

MODA ARENAS MEDIAS



	<i>D50</i>	
<i>Cantos y gravas</i>	>2	mm
<i>Arena muy gruesa</i>	1-2	mm
<i>Arena gruesa</i>	0,5-1	mm
<i>Arena media</i>	0,25-0,5	mm
<i>Arena fina</i>	0,125-0,25	mm
<i>Arena muy fina</i>	0,062-0,125	mm
<i>Fango</i>	<0,062	mm