


## ANALISIS GRANULOMETRICOS

MUESTRA: IP6

UTM X: 643291


UTM Y: 3233285



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.07 ( 100 %C)	0.1%	99.9%
n°25	0.71 mm	0.55 ( 100 %C)	0.6%	99.4%
n°35	0.5 mm	3.10 ( 0 %C)	3.7%	96.3%
n°60	0.25 mm	46.21 ( 0 %C)	49.9%	50.1%
n°80	0.18 mm	33.88 ( 0 %C)	83.8%	16.2%
n°120	0.125 mm	15.84 ( 0 %C)	99.7%	0.3%
n°230	0.063 mm	0.34 ( 0 %C)	100.0%	0.0%
Finos	<0,063 mm	0.00 ( 0 %C)	100.0%	0.0%

% FINOS	0.00%
% CASCAJO	0.62%
<b>D16</b>	0.431
<b>D50</b>	0.249
<b>D84</b>	0.179
<b>Media</b>	0.286
<b>σ</b>	0.126
<b>M. distribuc.</b>	0.305

### MODA ARENAS FINAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm