


ANALISIS GRANULOMETRICOS

MUESTRA: IP120

UTM X: 630901


UTM Y: 3199886



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 (0 %C)	0.0%	100.0%
n°10	2 mm	0.00 (0 %C)	0.0%	100.0%
n°18	1 mm	0.04 (50 %C)	0.0%	100.0%
n°25	0.71 mm	0.08 (50 %C)	0.1%	99.9%
n°35	0.5 mm	0.93 (25 %C)	1.1%	98.9%
n°60	0.25 mm	52.45 (0 %C)	53.5%	46.5%
n°80	0.18 mm	34.04 (0 %C)	87.5%	12.5%
n°120	0.125 mm	12.21 (0 %C)	99.8%	0.2%
n°230	0.063 mm	0.24 (0 %C)	100.0%	0.0%
Finos	<0,063 mm	0.00 (0 %C)	100.0%	0.0%

% FINOS	0.00%
% CASCAJO	0.29%
D16	0.428
D50	0.266
D84	0.187
Media	0.294
σ	0.120
M. distribuc.	0.307

MODA ARENAS MEDIAS



	<i>D50</i>	
<i>Cantos y gravas</i>	>2	mm
<i>Arena muy gruesa</i>	1-2	mm
<i>Arena gruesa</i>	0,5-1	mm
<i>Arena media</i>	0,25-0,5	mm
<i>Arena fina</i>	0,125-0,25	mm
<i>Arena muy fina</i>	0,062-0,125	mm
<i>Fango</i>	<0,062	mm