


## ANALISIS GRANULOMETRICOS

MUESTRA: IP98

UTM X: 635563


UTM Y: 3201615



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.06 ( 0 %C)	0.1%	99.9%
n°25	0.71 mm	0.70 ( 0 %C)	0.8%	99.2%
n°35	0.5 mm	3.39 ( 0 %C)	4.2%	95.8%
n°60	0.25 mm	42.96 ( 0 %C)	47.1%	52.9%
n°80	0.18 mm	24.71 ( 0 %C)	71.8%	28.2%
n°120	0.125 mm	25.80 ( 0 %C)	97.6%	2.4%
n°230	0.063 mm	2.30 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.06 ( 0 %C)	100.0%	0.0%

% FINOS	0.06%
% CASCAJO	0.00%
<b>D16</b>	0.431
<b>D50</b>	0.242
<b>D84</b>	0.154
<b>Media</b>	0.276
<b>σ</b>	0.139
<b>M. distribuc.</b>	0.293

### MODA ARENAS FINAS



	<i>D50</i>	
<i>Cantos y gravas</i>	>2	mm
<i>Arena muy gruesa</i>	1-2	mm
<i>Arena gruesa</i>	0,5-1	mm
<i>Arena media</i>	0,25-0,5	mm
<i>Arena fina</i>	0,125-0,25	mm
<i>Arena muy fina</i>	0,062-0,125	mm
<i>Fango</i>	<0,062	mm