


## ANALISIS GRANULOMETRICOS

MUESTRA: IP8


UTM X: 645979

UTM Y: 3231866



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.06 ( 100 %C)	0.1%	99.9%
n°25	0.71 mm	0.40 ( 100 %C)	0.5%	99.5%
n°35	0.5 mm	0.75 ( 0 %C)	1.2%	98.8%
n°60	0.25 mm	21.38 ( 0 %C)	22.6%	77.4%
n°80	0.18 mm	42.18 ( 0 %C)	64.8%	35.2%
n°120	0.125 mm	32.99 ( 0 %C)	97.8%	2.2%
n°230	0.063 mm	2.07 ( 0 %C)	99.8%	0.2%
Finos	<0,063 mm	0.17 ( 0 %C)	100.0%	0.0%

% FINOS	0.17%
% CASCAJO	0.46%
<b>D16</b>	0.323
<b>D50</b>	0.204
<b>D84</b>	0.148
<b>Media</b>	0.225
<b>σ</b>	0.087
<b>M. distribuc.</b>	0.235



## MODA ARENAS FINAS

	D50	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm