


ANALISIS GRANULOMETRICOS

MUESTRA: IP60


UTM X: 647214

UTM Y: 3208702



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 (0 %C)	0.0%	100.0%
n°10	2 mm	0.00 (0 %C)	0.0%	100.0%
n°18	1 mm	0.20 (25 %C)	0.2%	99.8%
n°25	0.71 mm	2.50 (10 %C)	2.7%	97.3%
n°35	0.5 mm	10.93 (0 %C)	13.6%	86.4%
n°60	0.25 mm	56.49 (0 %C)	70.1%	29.9%
n°80	0.18 mm	19.76 (0 %C)	89.9%	10.1%
n°120	0.125 mm	9.63 (0 %C)	99.5%	0.5%
n°230	0.063 mm	0.45 (0 %C)	100.0%	0.0%
Finos	<0,063 mm	0.05 (0 %C)	100.0%	0.0%

% FINOS	0.05%
% CASCAJO	0.30%
D16	0.488
D50	0.338
D84	0.201
Media	0.342
σ	0.144
M. distribuc.	0.344



MODA ARENAS MEDIAS

	D50	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm