


## ANALISIS GRANULOMETRICOS

MUESTRA: IP40


UTM X: 639905

UTM Y: 3221744



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.09 ( 50 %C)	0.1%	99.9%
n°25	0.71 mm	1.16 ( 50 %C)	1.2%	98.8%
n°35	0.5 mm	7.03 ( 0 %C)	8.3%	91.7%
n°60	0.25 mm	58.72 ( 0 %C)	67.0%	33.0%
n°80	0.18 mm	22.06 ( 0 %C)	89.1%	10.9%
n°120	0.125 mm	9.88 ( 0 %C)	98.9%	1.1%
n°230	0.063 mm	0.98 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.09 ( 0 %C)	100.0%	0.0%

% FINOS	0.09%
% CASCAJO	0.62%
<b>D16</b>	0.465
<b>D50</b>	0.321
<b>D84</b>	0.196
<b>Media</b>	0.327
<b>σ</b>	0.135
<b>M. distribuc.</b>	0.330



## MODA ARENAS MEDIAS

	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm