


## ANALISIS GRANULOMETRICOS

MUESTRA: IP15

UTM X: 637053


UTM Y: 3203191



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.04 ( 90 %C)	0.0%	100.0%
n°25	0.71 mm	0.00 ( 0 %C)	0.0%	100.0%
n°35	0.5 mm	0.12 ( 0 %C)	0.2%	99.8%
n°60	0.25 mm	17.70 ( 0 %C)	17.9%	82.1%
n°80	0.18 mm	35.59 ( 0 %C)	53.4%	46.6%
n°120	0.125 mm	41.82 ( 0 %C)	95.3%	4.7%
n°230	0.063 mm	4.74 ( 0 %C)	100.0%	0.0%
Finos	<0,063 mm	0.00 ( 0 %C)	100.0%	0.0%

% FINOS	0.00%
% CASCAJO	0.04%
<b>D16</b>	0.276
<b>D50</b>	0.187
<b>D84</b>	0.140
<b>Media</b>	0.201
<b>σ</b>	0.068
<b>M. distribuc.</b>	0.208

### MODA ARENAS FINAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm